



UP600

Intraoral Scanner



Clear Margin Line, High Precision And True Color

Truly restoring the intraoral color, with no interference of the saliva to scan the margin line clearly.



Multi Scanning Tips

Satisfying different kinds of complicated cases



Open Data Format

Output open format files, such as STL, PLY and OBJ, which is compatible with multiple design software, like UPCAD, exocad and 3Shape, etc.



Efficient And Precise Communication Tool Between Dentists And Patients

More convenient for the communication between dentists and patients with the intraoral teeth color truly restored by UP600 intraoral scanner and the precise visualized platform.



Filter The Soft Tissue Automatically

Prevent the interference of the redundant data during the scanning, reducing greatly of the scanning time.



Ease Of Use, Pick And Play

No need complicated setup, simpler and more considerate software interface to reduce the learning cost.
Pick and play, learning within 5 minutes quickly.




Shortcut To Digital Treatment



Best option to enter the digital dentistry era Latest intraoral scanning technology around the world Amazing begins with an instant start!

Combined intelligently with implantodontics, orthodontics and prosthodontics to replace the traditional impression taking

Upgrade to digital dentistry completely with higher accuracy



Detailed configuration	UP600
Dimension	275*49.5*47mm
Weight	450g
Depth Of Field	11mm
Scanning Height	0-17mm
Scanning Range	12*11mm
Accuracy	20μm
Scanning Speed	18-20 PFS
Scanning Head Anti-fogging Method	Hot wind heating
Scanning Head	45°, 17.4mm height 35°, 17.6mm height

UP3D | CONTACT US

Web: www.up3ds.com

Email: info@up3d.cn

Tel: +86-755-26983202

